




24-PIN PLASTIC SSOP(18.1x11.8)



(UNIT:mm)

ITEM	DIMENSIONS
D	11.80±0.10
E	18.10±0.10
HE	20.10±0.20
A	2.68±0.10
A1	0.125±0.05
A2	2.55
A3	0.25
e	0.80
bp	0.30 ^{+0.10} _{-0.05}
c	0.15 ^{+0.05} _{-0.01}
L	0.50
Lp	0.60±0.15
L1	1.00±0.10
x	0.16
y	0.10
theta	3° ^{+5°} _{-3°}
ZD	1.50

P24ML-80-JAA-1