





64-PIN PLASTIC SSOP (13.34 mm (525))



detail of lead end



NOTE

Each lead centerline is located within 0.10 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	$25.85^{+0.45}_{-0.2}$
B	0.75 MAX.
C	0.8 (T.P.)
D	0.35 ± 0.05
E	0.15 ± 0.05
F	2.3 MAX.
G	2.0 ± 0.1
H	13.8 ± 0.3
I	11.8 ± 0.1
J	1.0 ± 0.2
K	$0.20^{+0.10}_{-0.05}$
L	0.5 ± 0.2
M	0.10
N	0.10
P	$3^{\circ} + 7^{\circ}_{-3^{\circ}}$

P64GW-80-525A-3