


40-PIN PLASTIC ZIP (11.64 mm (475))



NOTE

Each lead centerline is located within 0.25 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	51.23 MAX.
F	0.50±0.10
G	0.25
H	2.54 (T.P.)
I	1.27 (T.P.)
J	0.85 MAX.
K	0.9 MIN.
M	10.5 MAX.
N	2.8±0.2
Q	12.07 MAX.
V	0.25 ^{+0.10} _{-0.05}
W	2.54 (T.P.)
Y	3.25±0.2

P40V-100-475A-2