


40-PIN PLASTIC SZIP (11.64 mm (475))



NOTE

Each lead centerline is located within 0.25 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	36.22 MAX.
F	0.40±0.10
G	0.25
H	1.778 (T.P.)
I	0.889 (T.P.)
J	0.85 MAX.
K	0.9 MIN.
M	10.45 MAX.
N	2.2±0.1
Q	12.0 MAX.
R	2°-6°
V	0.25 ^{+0.10} _{-0.05}
W	1.778 (T.P.)
Y	3.16±0.2

P40VF-70-475A-1