





352-PIN TAPE BGA (HEAT SPREADER TYPE) (35x35)



ITEM	MILLIMETERS
A	35.00±0.20
A1	23.00 MAX.
A2	23.00 MAX.
B	34.60±0.15
C	34.60±0.15
D	35.00±0.20
E	1.625
F	1.27 (T.P.)
G	0.60±0.10
H	0.80
J	1.40 ^{+0.30} _{-0.20}
K	0.15
L	ϕ 0.75±0.15
M	0.30
N	0.25 MIN.
P	0.10
Q	3.0
R	2.0
S	2.0
T	3.0
W	20.19
X	20.19
Y	C0.4
Z	0.20

P352N7-127-F6