






480-PIN TAPE BGA (HEAT SPREADER TYPE) (35x35)



⊕	φ M	Ⓜ	S	A	B
	φ P	Ⓜ	S		



ITEM	MILLIMETERS
A	35.00±0.20
A1	17.65 MAX.
A2	17.65 MAX.
D	35.00±0.20
E	1.625
F	1.27 (T.P.)
G	0.60±0.10
H	0.80
J	1.40 ^{+0.30} _{-0.20}
K	0.15
L	φ0.75±0.15
M	0.30
N	0.25 MIN.
P	0.10
Q	3.0
R	2.0
S	2.0
T	3.0
W	17.65
X	17.65
Y	C 0.40
Z	0.20

P480N7-127-F6