






504-PIN TAPE BGA (HEAT SPREADER TYPE) (40x40)



ITEM	MILLIMETERS
A	40.00±0.20
A1	23.00 MAX.
A2	23.00 MAX.
B	39.60±0.15
C	39.60±0.15
D	40.00±0.20
E	1.585
F	1.27 (T.P.)
G	0.60±0.10
H	0.80 ^{+0.20} _{-0.10}
J	1.40 ^{+0.30} _{-0.20}
K	0.15
L	φ 0.75±0.15
M	0.30
N	0.25 MIN.
P	0.10
Q	3.0
R	2.0
S	2.0
T	3.0
U	33.00±0.20
V	33.00±0.20
W	22.73
X	22.73
Z	0.20