




768-PIN TAPE BGA (HEAT SPREADER TYPE) (40x40)



Section B—B



ITEM	MILLIMETERS
D	40.00±0.20
E	40.00±0.20
w	0.15
e	1.00
A	1.30 ^{+0.30} _{-0.20}
A1	0.50±0.10
A2	0.8
A4	0.25 MIN.
b	0.60±0.10
x	0.10
y	0.15
y1	0.35
ZD	1.50
ZE	1.50

P768N7-100-H9