



### 93-PIN TAPE FBGA (12x9)



ITEM	MILLIMETERS
D	9.0±0.1
E	12.0±0.1
w	0.2
e	0.8
A	1.3±0.1
A1	0.16±0.05
A2	1.14
b	0.40±0.05
x	0.08
y	0.1
y1	0.2
ZD	0.9
ZE	0.8

P93F9-80-CR2