

JEITA Package Code

P-TQFP80-14x14-0.65

RENESAS Code




PTQP0080JA-A

Previous Code


TFP-80/TFP-80V

MASS[Typ.]

0.5g



Terminal cross section



Detail F

NOTE)

1. DIMENSIONS*1*AND*2* DO NOT INCLUDE MOLD FLASH
2. DIMENSION*3* DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	14	—
E	—	14	—
A ₂	—	1.00	—
H _D	15.3	15.6	15.9
H _E	15.3	15.6	15.9
A	—	—	1.20
A ₁	0.00	0.10	0.20
b _p	0.24	0.32	0.40
b ₁	0.24	0.30	0.36
c	0.12	0.17	0.22
c ₁	0.11	0.15	0.19
θ	0°	—	8°
[e]	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z _D	—	0.83	—
Z _E	—	0.83	—
L	0.4	0.5	0.6
L ₁	—	0.8	—