

JEITA Package Code

RENESAS Code

Previous Code



MASS[Typ.]

P-TQFP80-14x14-0.65


PTQP0080JA-A

TFP-80/TFP-80V

0.5g



Terminal cross section



Detail F

NOTE)

1. DIMENSIONS<sup>\*1</sup> AND<sup>\*2</sup> DO NOT INCLUDE MOLD FLASH
2. DIMENSION<sup>\*3</sup> DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	14	—
E	—	14	—
A <sub>2</sub>	—	1.00	—
H <sub>D</sub>	15.3	15.6	15.9
H <sub>E</sub>	15.3	15.6	15.9
A	—	—	1.20
A <sub>1</sub>	0.00	0.10	0.20
b <sub>p</sub>	0.24	0.32	0.40
b <sub>1</sub>	0.24	0.30	0.36
c	0.12	0.17	0.22
c <sub>1</sub>	0.11	0.15	0.19
θ	0°	—	8°
[e]	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z <sub>D</sub>	—	0.83	—
Z <sub>E</sub>	—	0.83	—
L	0.4	0.5	0.6
L <sub>1</sub>	—	0.8	—