

JEITA Package Code

RENASAS Code

Previous Code


MASS[Typ.]

P-TQFP80-14x14-0.65

PTQP0080JA-B

TFP-80F/TFP-80FV

0.5g




NOTE)

1. DIMENSIONS*1*AND*2*


DO NOT INCLUDE MOLD FLASH

2. DIMENSION*3*DOES NOT

INCLUDE TRIM OFFSET.



Terminal cross section



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	14	—
E	—	14	—
A ₂	—	1.00	—
H _D	15.8	16.0	16.2
H _E	15.8	16.0	16.2
A	—	—	1.20
A ₁	0.00	0.10	0.20
b _p	0.24	0.32	0.40
b ₁	—	0.30	—
c	0.12	0.17	0.22
c ₁	—	0.15	—
θ	0°	—	8°
\bar{e}	—	0.65	—
x	—	—	0.13
y	—	—	0.10
Z _D	—	0.83	—
Z _E	—	0.83	—
L	0.4	0.5	0.6
L ₁	—	1.0	—