





JEITA Package Code	RENESAS Code	Previous Code	MASS (Typ) [g]
SC-95 Modified	PTSP0006FA-A	TSOP-6 / TSOP-6V	0.012



Reference Symbol	Dimensions in millimeters		
	Min	Nom	Max
A	0.8	—	1.1
A ₁	0	—	0.1
A ₂	0.8	0.9	1.0
A ₃	—	0.25	—
b	0.2	0.3	0.4
c	0.1	0.15	0.25
D	2.8	2.95	3.1
E	1.45	1.6	1.75
e	—	1.0	—
HE	2.6	2.8	3.0
L	0.3	—	0.7
L ₁	0.1	—	0.5
L _P	0.2	—	0.6
x	—	—	0.05
y	—	—	0.05
Q	—	0.2	—