


32-PIN PLASTIC TSOP (II) (10.16mm(400))



NOTE

Each lead centerline is located within 0.21 mm of its true position (T.P.) at maximum material condition.

| ITEM | MILLIMETERS |
|------|---|
| A | 21.17 MAX. |
| B | 1.06 MAX. |
| C | 1.27 (T.P.) |
| D | 0.40±0.10 |
| E | 0.05±0.05 |
| F | 1.1 MAX. |
| G | 0.97 |
| H | 11.76±0.2 |
| I | 10.16±0.1 |
| J | 0.8±0.2 |
| K | 0.125 ^{+0.10} _{-0.05} |
| L | 0.5±0.1 |
| M | 0.21 |
| N | 0.10 |
| P | 5°±5° |

S32G5-50-7JD1-2