


48-PIN PLASTIC TSOP(II) (13.97 mm (550))



NOTE

Each lead centerline is located within 0.13 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	20.52 MAX.
B	1.06 MAX.
C	0.8 (T.P.)
D	0.30±0.10
E	0.05±0.05
F	1.1 MAX.
G	0.97
H	15.57±0.2
I	13.97±0.1
J	0.8±0.2
K	0.125 ^{+0.10} _{-0.05}
L	0.5±0.1
M	0.13
N	0.10
P	2° ^{+4°} _{-2°}

S48G8-80-7KF-2