





<b>JEITA Package Code</b>	<b>RENESAS Code</b>	<b>MASS (Typ.) [g]</b>
P-TSOP(2)52-8.89×10.79-0.40	PTSB0052LD-A	0.25



**Detail G**



**Detail F**

NOTE)  
 1. DIMENSIONS “\*1” AND “\*2”  
 DO NOT INCLUDE MOLD FLASH.  
 2. DIMENSIONS “\*3” DOES NOT  
 INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min.	Nom.	Max.
D	10.69	10.79	10.89
E	8.79	8.89	8.99
A <sub>2</sub>	—	1.00	—
H <sub>E</sub>	10.29	10.49	10.69
A	—	—	1.20
A <sub>1</sub>	0.05	0.125	0.20
b <sub>p</sub>	0.12	0.17	0.27
c	0.105	0.125	0.175
θ	0°	—	10°
e	—	0.40	—
x	—	—	0.08
y	—	—	0.10
Z	—	0.395	—
Z <sub>1</sub>	—	—	0.545
L	0.35	0.50	0.65