





70-PIN PLASTIC TSOP(II) (10.16 mm (400))



NOTES

1. Each lead centerline is located within 0.10 mm of its true position (T.P.) at maximum material condition.
2. "A" excludes mold flash. (Includes mold flash : 24.29mm MAX.)

ITEM	MILLIMETERS
A	23.45±0.10
B	0.85 MAX.
C	0.65 (T.P.)
D	0.24 ^{+0.08} _{-0.07}
E	0.1±0.05
F	1.2 MAX.
G	0.97±0.08
H	11.76±0.2
I	10.16±0.1
J	0.8±0.2
K	0.145 ^{+0.025} _{-0.015}
L	0.5
M	0.10
N	0.10
P	3° ^{+5°} _{-3°}
R	0.25
S	0.60±0.15

S70G5-65-7JG1-1