



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	14.00	—
E	—	14.00	—
v	—	—	0.15
A	—	—	0.93
A ₁	0.18	0.23	0.28
A ₂	—	0.30	—
e	—	0.50	—
e ₁	—	0.65	—
b	0.25	0.30	0.35
b ₁	0.27	0.30	0.33
x	—	—	0.08
y	—	—	0.10
Z _D	—	1.00	—
Z _E	—	1.00	—
D ₁	—	10.9	—
E ₁	—	10.9	—