



Reference Symbol	Dimensions in mm		
	Min	Nom	Max
D	9.90	10.00	10.10
E	9.90	10.00	10.10
A2	0.95	1.00	1.05
HD	11.80	12.00	12.20
HE	11.80	12.00	12.20
D1	6.40	6.50	6.60
E1	6.40	6.50	6.60
A	-	-	1.20
A1	0.05	0.10	0.15
bp	0.17	0.22	0.27
c	0.09	-	0.20
θ	0	3.5	7
e	0.50 BSC		
y	-	-	0.08
LP	0.45	0.60	0.75
L1	-	1.00	-

NOTES:

1. JEDEC compatible.
2. All dimensions are in mm and angles are in degrees.
3. Use ± 0.05 mm tolerance for all other dimensions.
4. Foot length is measured at gauge plane 0.25 mm above seating plane.