



TOP VIEW




BOTTOM VIEW



SIDE VIEW

COMMON DIMENSIONS:

D	16.30±0.15	E	17.00±0.15
T	1.90 max.	T0	0.50 max.
e1	0.80 BSC.	e2	1.20 BSC.
L1	0.70	W1	0.50
L2	0.80	W2	0.80
a1	2.25	b1	2.00
a2	3.05	b2	3.00
a3	1.45	b3	3.10
a4	2.45	b4	5.50
a5	6.50	b5	5.95



RECOMMENDED LAND PATTERN
(PCB Top View, NSMD Design)

NOTES:

1. All dimensions are in mm and angles are in degrees.
2. Use ±0.10 mm for the non-toleranced dimensions.
3. Numbers in () are for references only.