



Reference	Dimension in mm	
	Min	Max
A	1.35	1.75
D	4.80	5.00
E	3.80	4.00
A1	0.10	0.30
A2	1.32	1.55
HE	5.80	6.20
bp	0.31	0.51
c	0.10	0.25
e	1.27	
y	-	0.10
Lp	0.40	
θ	0	8

\* WITHOUT MOLD FLASH

NOTES:

1. JEDEC compatible.
2. All dimensions are in mm and angles are in degrees.