



TOP VIEW




BOTTOM VIEW



SIDE VIEW

COMMON DIMENSIONS:

D	22.53 ± 0.10	E	22.66 ± 0.10
T	1.47 ± 0.08		
eD1	1.20 BSC.	1/2 eD1	0.60 BSC.
1/2 eD2	0.70 BSC.	eD3	1.50 BSC.
eE1	1.20 BSC.	1/2 eE1	0.60 BSC.
eE2	1.70 BSC.	eE3	1.50 BSC.
L1	0.90 ± 0.10	W1	1.20 ± 0.10
L2	0.60 ± 0.05	W2	0.90 ± 0.10
A1	12.0 ± 1.0	A2	5.33 ± 0.50
A3	10.8 ± 1.0	A4	1.365 ± 0.10
B2	1.53 ± 0.05	B4	19.20 ± 0.20
B5	18.0 ± 0.20	B6	1.665 ± 0.10
C2	6.80 ± 0.50	D3	7.0 ± 0.50



RECOMMENDED LAND PATTERN  
(PCB Top View, NSMD Design)

NOTES:

1. All dimensions are in mm and angles are in degrees.