




CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PT771C	PRQP0208KD-A	FP-208 / FP-208V

Unit:mm



The pin1 is located in the hatching portion



Position dimension of cells (mm)	Z_W	27.1
	Z_L	25.25
	e_w	40.8
	e_L	37.9
	S_w	55
Thickness (mm)	H_1	8.7
	H_2	3
Number of cells	N_W	3
	N_L	8
Maximum storage No. IC/Tray		24
Maximum storage No. IC/Inner box		240
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack