




# CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PT539B	PLQP0080KD-A	FP-80TA / FP-80TAV

Unit:mm



The pin1 is located in the hatching portion



Position dimension of cells (mm)	$Z_W$	17.9
	$Z_L$	18.4
	$e_w$	25
	$e_L$	31
	$S_w$	55
Thickness (mm)	$H_1$	7.6
	$H_2$	2.5
Number of cells	$N_w$	5
	$N_L$	10
Maximum storage No. IC/Tray		50
Maximum storage No. IC/Inner box		500
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Non dry pack