


# CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
M095-51	PLQP0216LA-A	216P6R-B

Unit:mm



The pin1 is located in the hatching portion

Position dimension of cells (mm)	$Z_w$	25.9
	$Z_L$	27.5
	$e_w$	33.6
	$e_L$	35
Thickness (mm)	$H_1$	5.6
Number of cells	$N_w$	4
	$N_L$	8
Maximum storage No. IC/Tray		32
Maximum storage No. IC/Inner box		160
Material		Carbon PP
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C MAX
Packing form		Dry pack