


# CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
M095-61	PLQP0080KB-A	80P6Q-A

Unit:mm



The pin1 is located in the hatching portion

Position dimension of cells (mm)	$Z_w$	18.55
	$Z_L$	17
	$e_w$	16.5
	$e_L$	19
Thickness (mm)	$H_1$	5.6
Number of cells	$N_w$	8
	$N_L$	15
Maximum storage No. IC/Tray		120
Maximum storage No. IC/Inner box		600
Material		Carbon PP
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C MAX
Packing form		Dry pack