


CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
M095-45	PLQP0064GA-A	64P6U-A

Unit:mm



The pin1 is located in the hatching portion

Position dimension of cells (mm)	Z_w	20.05
	Z_L	22.4
	e_w	22.5
	e_L	23.2
Thickness (mm)	H_1	5.6
Number of cells	N_w	6
	N_L	12
Maximum storage No. IC/Tray		72
Maximum storage No. IC/Inner box		360
Material		Carbon PP
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C MAX
Packing form		Dry pack