


JEDEC TRAY

| Tray Code | RENESAS Code | Previous Code |
|-----------|--------------|---------------|
| PT579B | PVBG0064KB-A | — |
| | PVBG0081KA-A | — |

Unit:mm



The pin1 is located in the hatching portion

| | | |
|----------------------------------|-------|---|
| Position dimension of cells (mm) | Z_w | 8.15 |
| | Z_L | 7.9 |
| | e_w | 9.2 |
| | e_L | 8.8 |
| Thickness (mm) | H_1 | 7.62 |
| Number of cells | N_w | 14 |
| | N_L | 35 |
| Maximum storage No. IC/Tray | | 490 |
| Maximum storage No. IC/Inner box | | 4410 |
| Material | | Carbon PPE |
| Surface resistance | | Less than $1 \times 10^{11} \Omega / \square$ |
| Heat resistant temperature | | 125°C24h |
| Packing form | | Dry pack |