

| Magazine code     | MP016PC-2                   | Renesas code | Previous code | Maximum storage No. IC/Magazine | Maximum storage No. Magazine/Inner box | Maximum storage No. IC/Inner box | Packing form |
|-------------------|-----------------------------|--------------|---------------|---------------------------------|--|----------------------------------|--------------|
| Magazine material | PVC<br>(Polyvinyl chloride) | PRSP0010DB-A | 10P2N-A       | 70                              | 60                                     | 4200                             | Dry pack     |
|                   |                             | PRSP0014DD-A | 14P2N-A       | 50                              |  | 3000                             |              |
| Treatment         | Antistatic                  | PRSP0016DE-A | 16P2N-A       | 50                              |  | 3000                             |              |
| Length (mm)       | 550 +0<br>-1.5              | PRSP0020DA-A | 20P2N-A       | 40                              |  | 2400                             |              |
|                   |                             | PRSP0024GA-A | 24P2Q-A       | 50                              |  | 3000                             |              |

Unit:mm

