

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Mask ROM number	
-----------------	--

**740 FAMILY MASK ROM CONFIRMATION FORM**  
**SINGLE-CHIP MICROCOMPUTER M38504M6A-XXXSP/FP**  
**(Only for floppy disk orders)**

Receipt	Date :	
	Section head signature	Supervisor signature

Customer	Company name		Issuance signature	
	Phone		Submitted by	Supervisor
	Date Issued	Date :		

1. Confirmation

We will produce masks based on the mask files generated by the mask file generating utility. We shall assume the responsibility for errors only if the mask ROM data on the products we produce differs from this mask file. Thus, extreme care must be taken to verify the mask file in the submitted floppy disk.

The submitted floppy disk must be 3.5inch 2HD type (IBM format). And store only one mask file in a floppy disk.

Microcomputer type No.:  **M38504M6A-XXXSP**     **M38504M6A-XXXFP**

File code 

--	--	--	--	--	--	--	--

 (hexadecimal notation)

Mask file name 

--	--	--	--	--	--	--	--

 .MSK  
 (equal or less than eight characters)

Note : Write data to only ROM data area (addresses 808016 to FFFD16).

2. Mark specification

Mark specification must be submitted using the correct form for the package being ordered. Fill out the appropriate mark specification form (42P4B for M38504M6A-XXXSP, 42P2R for M38504M6A-XXXFP) and attach it to the mask ROM confirmation form.

**740 FAMILY MASK ROM CONFIRMATION FORM**  
**SINGLE-CHIP MICROCOMPUTER M38504M6A-XXXSP/FP**  
**(Only for floppy disk orders)**

3. Usage conditions

Please answer the following questions about usage for use in our product inspection:

(1) How will you use the X<sub>IN</sub>-X<sub>OUT</sub> oscillator?

- Ceramic resonator                       Quartz crystal  
 External clock input                       Other(  )

At what frequency?                      f(X<sub>IN</sub>) =  MHz

(2) Which function will you use the pins P<sub>41</sub>/X<sub>CIN</sub> and P<sub>40</sub>/X<sub>COU</sub>T as P<sub>41</sub> and P<sub>40</sub>, or X<sub>CIN</sub> and X<sub>COU</sub>T?

- Ports P<sub>40</sub> and P<sub>41</sub> function                       X<sub>CIN</sub> and X<sub>COU</sub>T function (external resonator)

(3) What is the power-supply voltage you will use?

V<sub>CC</sub>=  V

(4) Which mode will you use for main clock division ratio? (You can check multiple boxes)

- high-speed mode  
 middle-speed mode (except for the default mode reset)  
 low-speed mode

4. Comments