

2010年12月14日

新製品の主な仕様

品名	極性	パッケージ	ドレイン・ソース間電圧(V)	ドレイン電流(A)	許容損失(TC=25°C)(W)	オン抵抗(VGS=10V)(mΩ)	ゲート電荷量TYP.(nC)
NP35N04YUK *	Nch	HSON	40	35	97	5.5	38
NP35N055YUK *	Nch	HSON	55	35	97	7.0	38
NP60N04MUK *	Nch	TO-220	40	60	105	5.0	42
NP60N04NUK *	Nch	TO-262	40	60	105	5.0	42
NP60N04VUK *	Nch	TO-252	40	60	105	4.6	42
NP60N55MUK *	Nch	TO-220	55	60	105	6.7	42
NP60N55NUK *	Nch	TO-262	55	60	105	6.7	42
NP60N55VUK *	Nch	TO-252	55	60	105	6.3	42
NP75N04YUK *	Nch	HSON	40	75	138	3.3	61
NP75N055YUK *	Nch	HSON	55	75	138	5.3	61
NP89N04MUK *	Nch	TO-220	40	90	147	3.25	68
NP89N04NUK *	Nch	TO-262	40	90	147	3.25	68
NP89N04PUK *	Nch	TO-263	40	90	147	2.8	68
NP89N055MUK *	Nch	TO-220	55	90	147	4.35	68
NP89N055NUK *	Nch	TO-262	55	90	147	4.35	68
NP89N055PUK *	Nch	TO-263	55	90	147	3.95	68
NP90N04VUK *	Nch	TO-252	40	90	147	3.0	68
NP90N055VUK *	Nch	TO-252	55	90	147	4.1	68
NP90N04MUK *	Nch	TO-220	40	90	176	2.95	84

NP90N04NUK *	Nch	TO-262	40	90	176	2.95	84
NP90N055MUK *	Nch	TO-220	55	90	176	3.85	84
NP90N055NUK *	Nch	TO-262	55	90	176	3.85	84
NP100N04PUK *	Nch	TO-263	40	100	176	2.3	84
NP100N055PUK *	Nch	TO-263	55	100	176	3.2	84
NP109N04PUK *	Nch	TO-263	40	110	250	1.75	130
NP109N055PUK *	Nch	TO-263	55	110	250	2.3	130
NP110N04PUK *	Nch	TO-263	40	110	348	1.4	200
NP110N055PUK *	Nch	TO-263	55	110	348	1.75	200
NP160N04TUK *	Nch	TO-263-7p	40	160	250	1.5	130
NP160N055TUK *	Nch	TO-263-7p	55	160	250	2.1	130
NP180N04TUK *	Nch	TO-263-7p	40	180	348	1.05	200
NP180N055TUK *	Nch	TO-263-7p	55	180	348	1.4	200

* 開発中

以上