

May 14, 2013

LCD Modules with PCAP Touch Panels

Line-up (Prototype)

Screen Size	Resolution	Base LCD Module Part Number	Remarks
6.5"	1024×768	NL10276BC13-01	Standard Brightness
	640×480	NL6448BC20-30F	High Brightness
10.4"	1024×768	NL10276BC20-18D	Standard Brightness
		NL10276BC20-18F	High Brightness
	800×600	NL8060BC26-35D	Standard Brightness
12.1"	1024×768	NL10276BC24-21	Standard Brightness
		NL10276BC24-21F	High Brightness
15.0"	1024×768	NL10276BC30-39	SFT*、Standard Brightness
		NL10276BC30-34D	Standard Brightness
7.0" Wide	800×480	NL8048BC19-02	Standard Brightness
		NL8048BC19-02C	High Brightness
9.0" Wide	800×480	NL8048BC24-09D	SFT*、Standard Brightness
10.6" Wide	1280×768	NL12876AC18-03D	SFT*、Standard Brightness
12.1" Wide	1280×800	NL12880BC20-05D	SFT*、Standard Brightness

*SFT : Super Fine TFT. SFT is a proprietary high image quality technology of NLT Technologies