


| | | |
|---------------------------|---------------------|-----------------------|
| JEITA Package Code | RENESAS Code | MASS (Typ) [g] |
| P-LFBGA324-15x15-0.80 | PLBG0324GA-A | 0.70 |



| Reference Symbol | Dimensions in millimeters | | |
|------------------|---------------------------|-------|-------|
| | Min | Nom | Max |
| D | 14.90 | 15.00 | 15.10 |
| E | 14.90 | 15.00 | 15.10 |
| A | — | — | 1.70 |
| A1 | 0.35 | 0.40 | 0.45 |
| e | — | 0.80 | — |
| b | 0.45 | 0.50 | 0.55 |
| x1 | — | — | 0.15 |
| x2 | — | — | 0.08 |
| y | — | — | 0.10 |
| y1 | — | — | 0.20 |
| n | — | 324 | — |
| Z _D | — | 0.70 | — |
| Z _E | — | 0.70 | — |