




# 1155-PIN PLASTIC BGA (FLIP CHIP TYPE)(35x35)



detail of (A) part



AN AL AJ AG AE AC AA W U R N L J G E C A  
AP AM AK AH AF AD AB Y V T P M K H F D B

INDEX MARK

| ITEM | MILLIMETERS                            |
|------|--|
| D    | 35.00±0.10                             |
| RD   | 34.60±0.10                             |
| E    | 35.00±0.10                             |
| RE   | 34.60±0.10                             |
| w    | 0.20                                   |
| e    | 1.00                                   |
| SD   | 0.50                                   |
| SE   | 0.50                                   |
| A    | 3.61 <sup>+0.40</sup> <sub>-0.20</sub> |
| A1   | 0.45±0.10                              |
| A2   | 3.16                                   |
| b    | 0.60±0.10                              |
| x    | 0.10                                   |
| y    | 0.20                                   |
| y1   | 0.30                                   |
| ZD   | 1.00                                   |
| ZE   | 1.00                                   |

P1155S8-100-F7