




1521-PIN PLASTIC BGA (FLIP CHIP TYPE) (40x40)



Detail of (A) part



ITEM	MILLIMETERS
D	40.00±0.10
RD	39.60±0.05
E	40.00±0.10
RE	39.60±0.05
w	0.15
e	1.00
A	3.61±0.40
A1	0.45±0.10
A2	3.16
b	0.60±0.10
x	0.10
y	0.20
y1	0.30
ZD	1.00
ZE	1.00

P1521S8-100-N7