





JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-HLFQFP100-14x14-0.50	PLQP0100KC-A	100P6L-A	0.9g



NOTE)
 1. DIMENSIONS **1" AND **2"
 DO NOT INCLUDE MOLD FLASH.
 2. DIMENSION **3" DOES NOT
 INCLUDE TRIM OFFSET.



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	13.9	14.0	14.1
E	13.9	14.0	14.1
A ₂	—	1.4	—
H _D	15.8	16.0	16.2
H _E	15.8	16.0	16.2
A	—	—	1.7
A ₁	0	0.1	0.2
b _p	0.15	0.20	0.25
c	0.105	0.125	0.175
θ	0°	—	8°
Ⓢ	—	0.5	—
x	—	—	0.08
y	—	—	0.10
L	0.3	0.5	0.7
D ₂	—	8.0	—
E ₁	—	8.0	—