


Terminal cross section



Detail A (NTS)

## NOTE)

1. DIMENSIONS \*1\* AND \*2\* DO NOT INCLUDE MOLD FLASH
2. DIMENSION \*3\* DOES NOT INCLUDE TRIM OFFSET.
3. FLASH BURR ALLOW IN DEFINED AREA BY BROKEN LINE \*4\* THAT BE LESS THAN 0.5 FROM HEAT SINK EDGE.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
A	—	—	3.15
A <sub>1</sub>	0	0.05	0.10
A <sub>2</sub>	2.50	2.70	2.90
A <sub>4</sub>	0	—	0.20
b <sub>p</sub>	0.24	0.32	0.38
b <sub>1</sub>	—	0.30	—
c	0.23	0.27	0.32
c <sub>1</sub>	—	0.25	—
D	13.90	14.00	14.10
D <sub>1</sub>	13.30	13.50	13.70
H <sub>D</sub>	17.00	17.20	17.40
D <sub>3</sub>	9.30	9.50	9.70
D <sub>4</sub>	9.70	9.90	10.10
H <sub>E</sub>	17.00	17.20	17.40
E	13.90	14.00	14.10
E <sub>1</sub>	2.65	2.80	2.95
E <sub>2</sub>	2.35	2.50	2.65
E <sub>3</sub>	9.30	9.50	9.70
E <sub>4</sub>	9.70	9.90	10.10
ⓐ	—	0.65	—
L	0.65	0.80	0.95
θ	0°	—	8°
x	—	—	0.25
y	—	—	0.10