

JEITA Package Code

RENESAS Code

Previous Code






MASS[Typ.]

P-HWQFN24-4x4-0.50

PWQN0024KC-A

24PJS-A

0.03g



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	3.9	4.0	4.1
E	3.9	4.0	4.1
A_2	—	0.75	—
A	—	—	0.8
A_1	0	0	0.05
b_p	0.15	0.2	0.25
e	—	0.5	—
L_p	0.20	0.30	0.40
x	—	—	0.05
y	—	—	0.05
Z_D	—	0.75	—
Z_E	—	0.75	—
D_2	—	2.0	—
E_1	—	2.0	—