



109-PIN PLASTIC FBGA (11x11)



ITEM	MILLIMETERS
D	11.00±0.10
D1	10.40
E	11.00±0.10
E1	10.40
W	0.20
e	0.8
A	1.48±0.15
A1	0.35±0.10
A2	1.13
b	$\phi 0.50^{+0.05}_{-0.10}$
x	0.08
y	0.10
y1	0.20
ZD	1.10
ZE	1.10

P109S1-80-YHC