



| Reference Symbol | Dimension in Millimeters | | |
|------------------|--------------------------|------|------|
| | Min | Nom | Max |
| D | — | 13.0 | — |
| E | — | 13.0 | — |
| v | — | — | 0.15 |
| w | — | — | 0.20 |
| A | — | — | 1.40 |
| A1 | 0.35 | 0.40 | 0.45 |
| e | — | 0.80 | — |
| b | 0.45 | 0.50 | 0.55 |
| x | — | — | 0.08 |
| y | — | — | 0.10 |
| y1 | — | — | 0.2 |
| SD | — | — | — |
| SE | — | — | — |
| ZD | — | 0.90 | — |
| ZE | — | 0.90 | — |