

JEITA Package Code

RENESAS Code

Previous Code




MASS[Typ.]

P-LFQFP128-14x20-0.50


PLQP0128KB-A

128P6Q-A

0.9g



Terminal cross section



Detail F

NOTE)

1. DIMENSIONS *1" AND *2" DO NOT INCLUDE MOLD FLASH.
2. DIMENSION *3" DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	19.9	20.0	20.1
E	13.9	14.0	14.1
A ₂	—	1.4	—
H _D	21.8	22.0	22.2
H _E	15.8	16.0	16.2
A	—	—	1.7
A ₁	0.05	0.125	0.2
b _p	0.17	0.22	0.27
b ₁	—	0.20	—
c	0.09	0.145	0.20
c ₁	—	0.125	—
θ	0°	—	8°
Ⓜ	—	0.5	—
x	—	—	0.10
y	—	—	0.10
Z _D	—	0.75	—
Z _E	—	0.75	—
L	0.35	0.5	0.65
L ₁	—	1.0	—