




外形図 Outline drawing
 Renesasコード PLQP0080KJ-A

RDK-G-001674

1/1

ルネサスエレクトロニクス株式会社
 Renesas Electronics Corporation

| | | |
|----------------------|--------------|---------------|
| JEITA Package code | RENESAS code | MASS(TYP.)[g] |
| P-LFQFP80-12x12-0.50 | PLQP0080KJ-A | 0.49 |



| Reference Symbol | Dimension in Millimeters | | |
|------------------|--------------------------|-------|------|
| | Min. | Nom. | Max. |
| A | — | — | 1.60 |
| A ₁ | 0.05 | — | 0.15 |
| A ₂ | 1.35 | 1.40 | 1.45 |
| D | — | 14.00 | — |
| D ₁ | — | 12.00 | — |
| E | — | 14.00 | — |
| E ₁ | — | 12.00 | — |
| N | — | 80 | — |
| e | — | 0.50 | — |
| b | 0.17 | 0.22 | 0.27 |
| c | 0.09 | — | 0.20 |
| θ | 0° | 3.5° | 7° |
| L | 0.45 | 0.60 | 0.75 |
| L ₁ | — | 1.00 | — |
| aaa | — | — | 0.20 |
| bbb | — | — | 0.20 |
| ccc | — | — | 0.08 |
| ddd | — | — | 0.08 |