

JEITA Package Code

RENESAS Code

Previous Code


MASS[Typ.]

P-QFP64-14x14-0.80

PRQP0064GB-A


FP-64A/FP-64AV

1.2g




NOTE)

1. DIMENSIONS \*1\* AND \*2\* DO NOT INCLUDE MOLD FLASH
2. DIMENSION \*3\* DOES NOT INCLUDE TRIM OFFSET.



Terminal cross section



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	14	—
E	—	14	—
A <sub>2</sub>	—	2.70	—
H <sub>D</sub>	16.9	17.2	17.5
H <sub>E</sub>	16.9	17.2	17.5
A	—	—	3.05
A <sub>1</sub>	0.00	0.10	0.25
b <sub>p</sub>	0.29	0.37	0.45
b <sub>1</sub>	—	0.35	—
c	0.12	0.17	0.22
c <sub>1</sub>	—	0.15	—
θ	0°	—	8°
⓪	—	0.8	—
x	—	—	0.15
y	—	—	0.10
Z <sub>D</sub>	—	1.0	—
Z <sub>E</sub>	—	1.0	—
L	0.5	0.8	1.1
L <sub>1</sub>	—	1.6	—