



JEITA Package Code
P-QFP88-20x20-0.80


RENESAS Code
PRQP0088GA-A

Previous Code
FP-88/FP-88V

MASS[Typ.]
2.4g



Terminal cross section



Detail F

NOTE)
1. DIMENSIONS*1*AND*2*
DO NOT INCLUDE MOLD FLASH
2. DIMENSION*3*DOES NOT
INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	20	—
E	—	20	—
A ₂	—	2.70	—
H _D	22.9	23.2	23.5
H _E	22.9	23.2	23.5
A	—	—	3.05
A ₁	0.00	0.10	0.25
b _p	0.29	0.37	0.45
b ₁	—	0.35	—
c	0.12	0.17	0.22
c ₁	—	0.15	—
θ	0°	—	8°
e	—	0.8	—
x	—	—	0.15
y	—	—	0.10
Z _D	—	1.6	—
Z _E	—	1.6	—
L	0.5	0.8	1.1
L ₁	—	1.6	—