





|                       |              |               |            |
|-----------------------|--------------|---------------|------------|
| JEITA Package Code    | RENESAS Code | Previous Code | MASS[Typ.] |
| P-SOP14-5.3x10.1-1.27 | PRSP0014DD-A | 14P2N-A       | 0.2g       |



Detail F

NOTE)

1. DIMENSIONS  $*1$ " AND  $*2$ " DO NOT INCLUDE MOLD FLASH.
2. DIMENSION  $*3$ " DOES NOT INCLUDE TRIM OFFSET.

| Reference Symbol | Dimension in Millimeters |      |      |
|------------------|--------------------------|------|------|
|                  | Min                      | Nom  | Max  |
| D                | 10.0                     | 10.1 | 10.2 |
| E                | 5.2                      | 5.3  | 5.4  |
| $A_2$            | —                        | 1.8  | —    |
| $A_1$            | 0                        | 0.1  | 0.2  |
| A                | —                        | —    | 2.1  |
| $b_p$            | 0.35                     | 0.4  | 0.5  |
| c                | 0.18                     | 0.2  | 0.25 |
| $\theta$         | 0°                       | —    | 8°   |
| $H_E$            | 7.5                      | 7.8  | 8.1  |
| e                | 1.12                     | 1.27 | 1.42 |
| y                | —                        | —    | 0.1  |
| L                | 0.4                      | 0.6  | 0.8  |