


20-PIN PLASTIC SOP (9.53 mm (375))



NOTE

Each lead centerline is located within 0.12 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	13.00 MAX.
B	0.785 MAX.
C	1.27 (T.P.)
D	$0.40^{+0.10}_{-0.05}$
E	0.125 ± 0.075
F	2.9 MAX.
G	2.50 ± 0.2
H	10.3 ± 0.3
I	7.2 ± 0.2
J	1.6 ± 0.2
K	$0.15^{+0.10}_{-0.05}$
L	0.8 ± 0.2
M	0.12
N	0.10
P	$3^{\circ+7^{\circ}}_{-3^{\circ}}$

P20GT-50-375B-3