



71-PIN TAPE FBGA (11x7)



| ITEM | MILLIMETERS |
|------|-------------|
| D | 7.00±0.10 |
| E | 11.00±0.10 |
| w | 0.20 |
| A | 1.11±0.10 |
| A1 | 0.27±0.05 |
| A2 | 0.84 |
| e | 0.80 |
| b | 0.45±0.05 |
| x | 0.08 |
| y | 0.10 |
| y1 | 0.20 |
| ZD | 0.70 |
| ZE | 1.10 |

P71F9-80-BS1