



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	4.0	—
E	—	8.0	—
v	—	—	0.15
w	—	—	0.15
A	—	—	0.65
A_1	—	—	—
e	—	0.65	—
b	0.30	0.35	0.40
x	—	—	0.08
y	—	—	0.10
y_1	—	—	0.20
S_D	—	—	—
S_E	—	—	—
Z_D	—	0.375	—
Z_E	—	0.425	—