



外形図 Outline drawing
PVBG0924ZB-A


RDK-G-001636 1/1

ルネサス エレクトロニクス株式会社
Renesas Electronics Corporation


JEITA Package code	RENESAS code	MASS(TYP.)[g]
P-WFBGA924-12x12-0.38	PVBG0924ZB-A	0.25



注1) TOP面 SR開口断面



注2): チップ-基板表層断面
PKG反り含まず



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	11.925	12.00	12.075
E	11.925	12.00	12.075
w	—	—	0.20
e	—	0.5332	—
A	—	0.749	0.850
A1	0.125	0.16	0.195
A2	—	0.589	—
b	0.20	0.235	0.27
x	—	—	0.05
y	—	—	0.085
ZD	—	0.4014	—
ZE	—	0.4014	—