


CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
M095-63	PLQP0032GB-A	32P6U-A
	PLQP0048KB-A	48P6Q-A

Unit:mm



The pin1 is located in the hatching portion

Position dimension of cells (mm)	Z_w	17.5
	Z_L	18.25
	e_w	16.8
	e_L	15.5
Thickness (mm)	H_1	5.6
Number of cells	N_w	8
	N_L	18
Maximum storage No. IC/Tray		144
Maximum storage No. IC/Inner box		720
Material		Carbon PP
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C MAX
Packing form		Dry pack